

POLISHING STATION



Complete Metallography Polishing set up. Double disc variable speed, backed up by high torque, noiseless D.C. motors of 1/2 HP, with D.C drives, driving discs independently.

Disc dia. - 200 mm

Continuous stepless variable speed up to 1400 r.p.m., with digital R.P.M. indicators.

Anticorrosive- Thick - F.R.P. TOP Water faucet, built-in sink arrangement

Specimen storage drawer, paper (independent) storage cupboard.

Etching reagent, Consumable storage front racks.

Heavy duty warm air drier for immediate specimen drying, mounted on front. Quick paper change clamping ring.

GATHA Enterprises

3, Snehdeep Apts, Chintamaninagar, Sahakarnagar No. 2, Pune 411009 INDIA

Tel: 91-20-24227847 Mobile: 91-99 700 65875 Fax: 91-20-24215087

Email: gatha@vsnl.net , gathaent@dataone.in, gathaent@gmail.com